



TUMBLE NOW ROTATOR

Bubble Man's Tumble Now machine is an attractive and efficient machine for making dry sifted herbal extract of the highest purity.

The Tumble Now is constructed of top quality materials and contains no plastic parts.

The Tumble Now is an electric powered, rotating, dry floral essence extractor with dual screen meshes. Features include a pull-out dry sift collection drawer and a double-hinged lid. The motor and wiring are fully enclosed and accessible through a vented access plate.

How it works

Once the Tumble Now is switched on, the motor will rotate the mesh cylinder with the material placed inside. Herbal extract will sift through the 125 micron stainless steel mesh of the cylinder, and can be collected on the 70 micron flat screen frame, or further scraped through the screen onto the black acrylic collection plate below with the card provided.



For best results

Use aged, dry plant material in a low humidity environment. We recommend wiping the interior of the unit and parts to remove any dust prior to initially using the Tumble Now machine.

Operation Instructions

1. Carefully take the tumbler and parts out of the box, and remove all packaging material.
2. Take the flat screen and black acrylic collection plate out of their box and remove protective film from acrylic plate.
3. Open drawer at base of the tumbler and place the black acrylic plate down first.
4. Then place the flat screen frame on top of the plate and close drawer.
No other assembly, tools or adjustments required.
5. Plug into wall power outlet.
6. Fill the cylinder with up to 150 grams / 5 ounces of plant material.
7. Put the circular metal end cap on to seal the cylinder.
Note: this is held on using strong magnets.
8. Place tumbling cylinder back into unit.
9. Press power button, and check after 10 minutes. Run for additional 5 minute increments as necessary, monitoring your progress with a magnifying glass.



Electrical 6 volt DC motor with AC-DC converter.

The motor is guaranteed for a minimum of 1000 operating hours.

Cylinder Rotating Speed: 36 RPM

Capacity Approximately 150 grams (5 ounces) of plant material can be processed at a time.

Dimensions Outside Dimensions (approximate): 18" x 11" x 11.25"

Questions? Call 1.866.635.8464